

Ultraclean CBX Technical Data Sheet

Description:

Ultraclean CBX is a strong alkaline detergent for use in ultrasonic baths.

- Aqueous based product
- Heavy oil and carbon contaminant removal
- Reduces surface tension, enhances ultrasonic cleaning performance
- Contains de-foaming agent

Applications

Ultraclean CBX is used to remove heavy oil and carbon from parts and components in manufacturing and processing industries. (Not suitable for processing aluminium or other soft metals. Instead, please use Ultraclean SA)

Directions for Use

Add 20-50ml of Ultraclean CBX per 1 Litre of water in the ultrasonic cleaner. Do not mix with other solutions.

The required dosage will depend on your cleaning application and the level of contamination. Items should be rinsed with water and dried immediately after processing.

Technical Data

These figures are typical and should not be interpreted as specifications, refer to MSDS for details.

Characteristic	Value/Description
Appearance	Light brown liquid
Odour	Characteristic
pH-value at 20°C	13
Relative density	1.05



Available in:

- 6x1L box (Part no. F5000401)
- 30 Litre Drum (Part no. F5000301)

Disposal

When diluted to concentration of 5% or less, Ultraclean CBX is not hazardous to aquatic organisms and may be safely disposed of down the drain. Refer to regional or national regulations.

Storage

12 months when stored in a cool, dark environment.